

### Introduction

Power failures tend to cause a domino effect of disruptions, resulting in system failures and data loss, as well as damage to servers and equipment. This article describes how to use the [MP5515](#) to protect solid-state drives (SSDs) against sudden power failure.

There are three main issues if an SSD experiences a power failure:

- Loss of user-written data
- Loss of flash memory conversion layer mapping information
- Increased risk for physical damage. When the SSD is subjected to strong vibrations or a sudden power failure during the reading or writing process, the SSD's head can scratch the medium

### Energy Storage and Release Management with the MP5515

The [MP5515](#) is an input power conditioning PMIC that provides a compact, efficient backup energy management solution for enterprise SSDs, non-volatile dual in-line memory modules (NVIDMMs), and other applications. This IC includes tantalum capacitors, which are more reliable than supercapacitors. Additionally, the [MP5515](#) can detect the circuit's health to provide data security.

Based on the high-voltage energy storage method, the [MP5515](#) integrates boost, buck, input current limiting, and input reverse current blocking protections, as well as power failure monitoring functions. Only a single inductor and small feedback voltage resistance are required to enable system start-up.

During normal operation, the [MP5515](#) stores energy in high-voltage capacitors. In the event of a power failure, the device transfers energy from the storage capacitor to the bus voltage line. This energy transfer provides the system with a stable, backup power supply.


Other key features of the [MP5515](#) include:

- Wide 2.7V to 18V operating input voltage ( $V_{IN}$ ) range
- Up to 32V of configurable storage voltage
- Up to 6A of configurable input current ( $I_{IN}$ ) limit
- 5A buck load capability
- Adjustable slew rate for the rising  $V_B$  voltage
- Input current limiting with an integrated 14m $\Omega$  MOSFET
- Input over-voltage protection (OVP)
- Reverse-current protection (RCP)
- Input power failure indicator
- Backup capacitor health testing
- Integrated voltage, current, and temperature detection

The [MP5515](#) effectively minimizes the use of standard external components, and is available in a QFN-30 (5mmx5mm) package. It also provides I<sup>2</sup>C communication and an analog-to-digital converter (ADC). We will discuss the strategic advantages of the [MP5515](#) for energy storage and release management in detail below.

### Response to Sudden Power Failure

To minimize data loss, the [MP5515](#) is designed with a shutdown detection circuit that includes a high energy density capacitor. Figure 1 shows an integrated solution with the [MP5515](#).




**Figure 1: Integrated Solution with the MP5515**

The e-fuse module continuously monitors the SSD’s supply voltage. If this power supply drops to a set threshold, this signals a sudden external power failure event, and the e-fuse cuts off the power supply circuit. The sufficient power protection window gives enough time for data to be flashed from the cache to NAND. The capacitor then forms a discharge path; once the power is turned on again, the capacitor charges quickly.

**E-Fuse and Integrated, Bidirectional Buck-Boost**

When the system is sufficiently powered, the diode, buck, and boost are required from the input to the output of the separation circuit. Using five (or more) FETs and diodes increases power consumption while reducing efficiency. Generally, the [MP5515](#) only requires its integrated 14mΩ MOSFET for input current limiting.

In the event of an abnormal power failure, the [MP5515](#)’s integrated, bidirectional buck-boost converter has three FETs, which help reduce power loss while minimizing the total solution size. Figure 2 shows the [MP5515](#)’s efficiency curve in standby power mode when  $V_B$  is 7.5V.



**Figure 2: MP5515 Buck Efficiency Curve ( $V_B = 7.5V$ )**

Figure 3 shows the [MP5515](#) efficiency curve in standby power mode when  $V_B$  is 10V.




Figure 3: MP5515 Buck Efficiency Curve ( $V_B = 10V$ )

### Smaller Energy Storage Capacitors

According to the law of conservation of energy, when the energy storage capacitor voltage increases, its capacity is significantly reduced. The [MP5515](#) can increase the energy storage capacitor’s voltage up to 36V. Under a consistent energy demand, the capacitance can drop to as low as 2.5mF and have a reduced ESR. Under normal conditions, the energy storage capacitor has a voltage rating of 18V and a capacitance of 8.4mF.

### Highly Integrated Chip

Traditional solutions typically require matching at least four chips with complex peripheral hardware circuits and software technologies. The [MP5515](#) provides an integrated solution using a single inductor. Figure 4 shows the typical application circuit of the [MP5515](#).




Figure 4: MP5515 Typical Application Circuit and Required External Components

Figure 5 shows that the [MP5515](#) requires a minimal number of external components.




Figure 5: MP5515 PCB Layout

### Capacitive Health Detection

During SSD use, the capacitor ages and energy storage capacitance is reduced over time due to a large number of charging and discharging processes. To address this, the [MP5515](#) integrates capacitive health testing, where an external resistor connected from STRG to RTEST discharges the energy storage capacitor. The detected results are stored in the data register for the microcontroller, and can be read via the I<sup>2</sup>C interface.

Engineers can easily derive and calculate the energy storage capacitance according to the energy conservation formula to determine whether a capacitor should be replaced. Figure 6 shows the calculations for  $V_{INITIAL(DATA2)}$ ,  $V_{FINAL(DATA1)}$ , and the time counter, which are used to estimate the capacitance.




Figure 6: MP5515 Energy Storage Capacitor Detection Circuit Power

### Fast Transition to Backup Mode

Buck mode supports a maximum current limit function to limit the released current. In each buck mode switching cycle, the high-side MOSFET (HS-FET) does not turn on until the inductor current drops to the valley current limit. Constant-on-time (COT) control is used when the bidirectional converter releases the energy from the storage capacitors. This minimizes the voltage drop while the device transitions from charge mode to backup mode.

Figure 7 shows the backup power release process for VIN shutdown under different bus loads (where the VB load is 1A or 5A).




Figure 7: MP5515 System Shutdown

Figure 8 shows a closer look at the [MP5515](#)'s shutdown waveforms.



Figure 8: MP5515 Shutdown Transition Waveforms

Figure 9 shows that the [MP5515](#) also supports a wide 270kHz to 1.25MHz frequency range that supports various inductances.




Figure 9: MP5515's Wide Frequency Range

### Flexible Parameter Configuration via I<sup>2</sup>C Communication

The [MP5515](#) is highly customizable through the MPS's I<sup>2</sup>C GUI, and can implement robust features. In addition to the key features of the [MP5515](#) that we previously discussed, these features for flexible parameter configuration include:


- Energy storage capacitor health detection
- A 10-bit ADC with voltage, current, and temperature detection
- Energy storage boost
- Adjustable buck frequency
- Input recovery control
- System status monitoring
- Interrupt mask control

Figure 10 shows the communication kit (the [EVKT-USBI2C-02](#)).



**Figure 10: MPS EVKT-USBI2C-02 Communication Interface**

Figure 11 shows a power failure protection circuit using the [MP5515](#), [MP5470](#), and [MP28167-A](#).



**Figure 11: Power Failure Protection Circuit**

In addition to the [MP5515](#), MPS also offers the [MP5505](#), [MP5512](#), and other shutdown protection solutions.

**Conclusion**

Protecting SSDs against sudden power failure is critical to maintain the stable operation of many devices connected in series. MPS continues to expand on this market by launching energy storage solutions, which are customized for numerous applications that require long-term stable operation. These applications include transportation, network communications, factory automation equipment, surveillance systems, smart in-vehicle monitoring, and data centers. Explore MPS’s energy management solutions, such as the [MP5515](#), [MP5470](#), [MP28167-A](#), [MP5505](#), and [MP5512](#), and learn how we can help power and protect your device.