

**BUREAU VERITAS**  
Certification



## 成都芯源系统有限公司

注册地址：四川省成都高新区西部园区出口加工区

运营地址：中国四川省成都市高新综合保税区科新路 8 号附 3 号

统一社会信用代码：915101007622864123

此份为多场所证书，各分场所见证书附页

必维认证集团认证控股有限公司英国分公司

确证上述单位的管理体系已经评审

并确认符合下列管理体系标准全部适用条款的要求

## ISO 14001:2015

体系覆盖范围

大电流管理和模拟混合信号集成电路测试

最初认证周期起始日期：2017 年 2 月 7 日（颁证机构：莱茵检测认证服务（中国）有限公司）  
上一周期的到期日：2020 年 2 月 6 日  
认证/再认证审核日期：2019 年 12 月 9 日  
本次认证/再认证周期起始日期：2020 年 2 月 14 日

在证书持有者之管理体系持续符合要求的运行条件下，本证书至下述日期有效：  
2023 年 2 月 6 日

证书号：CNBJ313470-UK

版本号：No.1，批准日期：2020 年 2 月 14 日

必维认证集团认证控股有限公司英国分公司  
授权代表

认证机构地址：5<sup>th</sup> Floor, 66 Prescot Street, London E1 8HG, United Kingdom  
当地办公室地址：中国上海市黄浦区外马路1288号综合楼四层B室，邮编：200011

需进一步澄清本证书认证范围及此管理体系要求的适用性，可直接向持证者查询。

要查证本证书之有效状态请电：(+86 21 23190329)

获证组织必须定期接受监督审核并经审核合格此证书方继续有效。本证书信息可在国家认证认可监督管理委员会官方网站([www.cnca.gov.cn](http://www.cnca.gov.cn))上查询。





BUREAU VERITAS  
Certification



## 成都芯源系统有限公司

### ISO 14001:2015

#### 体系覆盖范围

场所名称	场所地址	场所认证范围
成都芯源系统有限公司	四川省成都高新区西部 园区出口加工区	仅为注册地址
成都芯源系统有限公司	中国四川省成都市高新 综合保税区科新路 8 号附 3 号	大电流管理和模拟混合信号集成电路 测试
成都芯源系统有限公司	中国四川省成都市高新 综合保税区科新路 8 号附 6 号 3 号厂房	大电流管理和模拟混合信号集成电路 测试

证书号: CNBJ313470-UK

版本号: No.1, 批准日期: 2020 年 2 月 14 日

张利军

必维认证集团认证控股有限公司英国分公司  
授权代表



认证机构地址: 5<sup>th</sup> Floor, 66 Prescot Street, London E1 8HG, United Kingdom  
当地办公室地址: 中国上海市黄浦区外马路1288号综合楼四层B室, 邮编: 200011

需进一步澄清本证书认证范围及此管理体系要求的适用性, 可直接向持证者查询。

要查证本证书之有效状态请电: (+86 21 23190329)

获证组织必须定期接受监督审核并经审核合格此证书方继续有效。本证书信息可在国家认证认可监督管理委员会官方网站([www.cnca.gov.cn](http://www.cnca.gov.cn))上查询。



**BUREAU VERITAS**  
Certification



## **CHENGDU MONOLITHIC POWER SYSTEMS CO., LTD.**

REGISTERED ADDRESS: EXPORT PROCESSING ZONE, WESTERN PARK, HI-TECH ZONE,  
CHENGDU CITY, SICHUAN PROVINCE

OPERATION ADDRESS: NO.8-3, KEXIN ROAD, HI-TECH COMPREHENSIVE BONDED ZONE,  
CHENGDU CITY, SICHUAN PROVINCE 611731, P.R. CHINA

Unified social credit code: 915101007622864123

This is a multi-site certificate, additional site(s) are listed on the next page(s).

*Bureau Veritas Certification Holding SAS - UK Branch certifies that the  
Management System of the above organisation has been audited and found to  
be in accordance with the requirements of the management system standards  
detailed below*

### **ISO 14001:2015**

*Scope of certification*

#### **Test of Power Management and Analog/Mixed Signal Integrated Circuits**

Original cycle start date: **2 FEBRUARY 2017** (Issuing Certification Body: TUV Rheinland)  
Expiry date of previous cycle: **6 FEBRUARY 2020**  
Certification / Recertification audit date: **9 DECEMBER 2019**  
Certification / Recertification cycle start date: **14 FEBRUARY 2020**

Subject to the continued satisfactory operation of the organisation's Management System,  
this certificate expires on: **6 FEBRUARY 2023**

Certificate No. : **CNBJ313470-UK**

Version: **No.1**, Revision date: **14 FEBRUARY 2020**

*Signed on behalf of BVCH SAS UK Branch*

Certification body address: 5<sup>th</sup> Floor, 66 Prescot Street, London E1 8HG, United Kingdom.

Local office address: Rm. B, F4, No.1288, Waima Road, Huangpu District, Shanghai, China. 200011.

Further clarifications regarding the scope of this certificate and the applicability of the management system requirements may be obtained by consulting the organisation.

To check this certificate validity please call: (+86 21 23190329)

Certified organisation has to accept and pass regular surveillance audits, then this certificate can be continuously valid. Information of this certificate may be obtained by visiting CNCA website ([www.cnca.gov.cn](http://www.cnca.gov.cn)).



**BUREAU VERITAS**  
Certification



## CHENGDU MONOLITHIC POWER SYSTEMS CO., LTD.

### ISO 14001:2015

#### Scope of certification

<u>Site Name/Location</u>	<u>Site Address</u>	<u>Site Scope</u>
Chengdu Monolithic Power Systems Co., Ltd.	Export Processing zone, western park, Hi-Tech Zone, Chengdu City, Sichuan Province	Only Registered Address
Chengdu Monolithic Power Systems Co., Ltd.	No.8-3, Kexin Road, Hi-Tech Comprehensive Bonded Zone, Chengdu City, Sichuan Province 611731, P.R. China	Test of Power Management and Analog/Mixed Signal Integrated Circuits
Chengdu Monolithic Power Systems Co., Ltd.	Plant 3, No.8-6, Kexin Road, Hi-Tech Comprehensive Bonded Zone, Chengdu City, Sichuan Province 611731, P.R. China	Test of Power Management and Analog/Mixed Signal Integrated Circuits

Certificate No. : CNBJ313470-UK

Version: No.1, Revision date: 14 FEBRUARY 2020

*[Handwritten signature]*

Signed on behalf of BVCH SAS UK Branch



Certification body address: 5<sup>th</sup> Floor, 66 Prescott Street, London E1 8HG, United Kingdom.

Local office address: Rm. B, F4, No.1288, Waima Road, Huangpu District, Shanghai, China. 200011.

Further clarifications regarding the scope of this certificate and the applicability of the management system requirements may be obtained by consulting the organisation.

To check this certificate validity please call: (+86 21 23190329)

Certified organisation has to accept and pass regular surveillance audits, then this certificate can be continuously valid. Information of this certificate may be obtained by visiting CNCA website ([www.cnca.gov.cn](http://www.cnca.gov.cn)).