


Scalable Power Solutions for Zynq UltraScale+ MPSoC

Last update
June 20, 2018



X18834-011817




Design Specifications – UC1-3 Always ON 5 Rails (Modules)

Rail#	Rails	Vout	max Load	MPS part#	Footprint
1	VCCINT, VCCINT_VCU, VCCINT_IO, VCCBRAM, VCC_PSINTF, VCC_PSINTLP, VCC_PSINTFP_DDR	0.85/0.9V +/- 5%	3A to 10A	MPM3695A-10	QFN-45 (8mmx8mmx1.6mm)
			10A to 20A	MPM3695-25	QFN-59 (10mmx12mmx4mm)
			20A to 36A	MPM3695-25 (2x)	QFN-59 (10mmx12mmx4mm) 2x modules
2	VCC_PSAUX, VCC_PSDDR_PLL, VCC_PSADC, VCCAUX, VCCAUX_IO, VCCADC, DDR_VPP1, VCCO(0..)HDIO, VCCO(0..)HPPIO	1.8V+/-3%	2A	MPM3620A	QFN20 (3x5x1.6mm)
3	no MGT, VCC_PSPLL, VCC_VCU_PLL	1.2V+/-3%	0.6A	MPM3606A	QFN20 (3x5x1.6mm)
4	VCCO_PSDDR, DDR_VDD2, DDR_VDDQ, VCCO(0..)HDIO	USER (1.1- 1.5V)	1A	MPM3610A	QFN20 (3x5x1.6mm)
5	VCCO_PSIO[0..2], VCCO(0..)HDIO	USER (1.8- 3.3V)	1A	MPM3610A	QFN20 (3x5x1.6mm)



Block Diagram – UC1-3 Always ON 5 Rails (Modules)



Power on sequence 1 2 3




MPS product selector – UC1-3 Always ON 5 Rails (Modules)

5 RAILS (MODULES)	Voltage (V)	Toleran ce	ZU2CG	ZU2EG (A)	ZU3CG	ZU3EG	ZU4CG	ZU4EG	ZU4EV	ZU5CG	ZU5EG	ZU5EV	ZU6CG	ZU6EG	ZU7CG	ZU7EG	ZU7EV	ZU9CG	ZU9EG	ZU11EG	ZU15EG	ZU17EG	ZU19EG
Rail 1	0.85/0.9	+/-3%	MPM3695A-10 (max 10 A)					MPM3695-25 (max 20 A)								2x MPM3695-25 (max 40 A)							
Rail 2	1.8	+/-3%*	MPM3620A (max 2 A)																				
Rail 3	1.2	+/-3%*	MPM3606A (max 0.6 A)																				
Rail 4	USER (1.1-1.5)		MPM3610A (max 1 A)																				
			MPM3620A (max 2 A)																				
			MPM3632C (max 3 A)																				
Rail 5	USER (1.8-3.3)		MPM3610A (max 1 A)																				
			MPM3620A (max 2 A)																				
			MPM3632C (max 3 A)																				


Product Overview

Through the use of MPS' innovative single-step assembly process, our modules have superior performance and inherent reliability by eliminating unnecessary assembly steps and minimizing external components. They are easy to use and rework due to our standard QFN packaging, which eliminates some of the disadvantages that may have been associated with BGA or NDY packages. As a result, MPS modules are also inherently more cost effective.




- **Benefits**
 - Ease of design
 - Simple manufacturing
 - Small footprint
 - High performance
 - Cost effective

Lead-frame with all components (regulator IC, inductor, and other passives) integrated onto the same lead frame. Utilizing standard IC assembly process, packaging, and test equipment to cost effectively mass produce. Our modules can be easily implemented during system circuit development; they are easier to test, solder, and rework; No expensive Optical alignment BGA rework machines and X-ray inspection required.




Schematics (Typical)




- Solution footprint: 52mm²
- External Components: 7
- Efficiency: 88% (Vin=12V, Vout=3.3V, Io=0.4A)

Layout guidelines




Top Layer



Bottom Layer

Schematics (Typical)




- Solution footprint: 52mm²
- External Components: 7
- Efficiency: 89% (Vin=12V, Vout=3.3V, Io=1A)

Layout guidelines




Top Layer




Bottom Layer

Schematics (Typical)




- Solution footprint: 52mm²
- External Components: 7
- Efficiency: 82% ($V_{in}=12V$, $V_{out}=1.8V$, $I_o=1A$)

Layout guidelines




Top Layer




Bottom Layer



Schematics



Layout guidelines



Top Layer




PCB area 55mm²

Caps included in area calculations:


Output Caps 1x 22µF 0805

Input Caps: 2x 0603 on PCB bottom



Schematics



Efficiency vs. Load Current




Layout guidelines




Solution size: 230mm²

Layout guidelines




Schematics (Typical)




- Solution footprint: 19mm^2
- External Components: 5

Layout guidelines



Schematics (Typical)



Layout guidelines

- For Rails: V_{REF}
- Solution footprint: 4.5mm^2
- External Components: 3

- Maximize coverage of ZU+ family with wide choice of products from MPS
- Use of integrated modules for simplified design and PCB layout
- High Efficiency
- Cost effective
- Smallest Solution Size
- Minimum External Components
- Fast Transient Response and minimum ripple
- Modules are fully tested



Thank you

For additional information please contact

Thomas Fenn at thomas.fenn@monolithicpower.com

or MPS Reference Design Team

at referencedesign@monolithicpower.com

For general information

<http://www.monolithicpower.com>